


DACLON NYLON

DACLON
NYLON



Type	Monofilament
Composition	Extrusion of polyamide 6.0 or 6.6
Coating	None
Colour	Blue Black
Tissue reaction	Minimal
Absorption	Non absorbable, gradually encapsulated by connective tissue. The thread mass diminishes, approximately 10% a year by rupture of chemical links (hydrolytic action).
Presentation	Box with 12 sutures

*For quality
&
safety*

smi

www.sutures.be

DACLON

NYLON

CHARACTERISTICS

- ✓ High tensile strength, non absorbable
- ✓ Synthetic
- ✓ Monofilament with microscopic uniform diameter
- ✓ Pliability and softness
- ✓ Hermetically sealed packing

BENEFITS

- Excellent and permanent tissue support
- Minimal tissue reaction
- Soft passage through the tissues without sawing, tissue drag and trauma
- Absence of capillarity (no support of bacterial growth)
- Excellent knot tie down
- Good handling properties
- Easy and secure knotting
- Guaranteed seal and product sterility

INDICATIONS General soft tissue closing and/or ligation

Daclon Blue

especially in Skin closure
General surgery
Plastic surgery
Gastrointestinal surgery
Gynaecology
Obstetrics
Orthopaedics


Daclon Black

especially in Plastic surgery
Ophthalmic surgery



Round bodied taper point

1/2 circle



		Metric	USP	Length		Order number	
HR 16 mm		1	5/0	75 cm	<i>black</i>	9100116	
		1.5	4/0	75 cm	<i>blue</i>	9150116	
	HR 20 mm		0.7	6/0	75 cm	<i>black</i>	9070120
			1	5/0	75 cm	<i>black</i>	9100120
			1.5	4/0	75 cm	<i>blue</i>	9150120
			2	3/0	75 cm	<i>blue</i>	9200120
		3	2/0	75 cm	<i>blue</i>	9300120	





Reverse cutting

3/8 circle



		Metric	USP	Length		Order number
DS 12 mm		0.5	7/0	75 cm	<i>black</i>	9051512
		0.7	6/0	75 cm	<i>black</i>	9071512
		1	5/0	75 cm	<i>black</i>	9101512
		1.5	4/0	75 cm	<i>blue</i>	9151512
DS 12 mm Easy Pass		0.7	6/0	50 cm	<i>black</i>	9071512P
		1	5/0	50 cm	<i>black</i>	9101512P
		1.5	4/0	50 cm	<i>blue</i>	9151512P
DS 16 mm		0.7	6/0	45 cm	<i>black</i>	9071516-45
		0.7	6/0	75 cm	<i>black</i>	9071516
		1	5/0	45 cm	<i>black</i>	9101516-45
		1	5/0	75 cm	<i>black</i>	9101516
		1.5	4/0	45 cm	<i>blue</i>	9151516-45
		1.5	4/0	75 cm	<i>blue</i>	9151516
		2	3/0	75 cm	<i>blue</i>	9201516
DS 16 mm Easy Pass		0.7	6/0	50 cm	<i>black</i>	9071516P
		1	5/0	50 cm	<i>black</i>	9101516P
		1.5	4/0	50 cm	<i>blue</i>	9151516P
DS 16 mm black		1	5/0	75 cm	<i>black</i>	9101516VB
DS 19 mm		1	5/0	45 cm	<i>black</i>	9101519-45
		1	5/0	75 cm	<i>black</i>	9101519
		1.5	4/0	45 cm	<i>blue</i>	9151519-45
		1.5	4/0	75 cm	<i>blue</i>	9151519
		1.5	4/0	90 cm	<i>blue</i>	9151519-90
		2	3/0	45 cm	<i>blue</i>	9201519-45
		2	3/0	75 cm	<i>blue</i>	9201519
		2	3/0	90 cm	<i>blue</i>	9201519-90
		3	2/0	75 cm	<i>blue</i>	9301519

Reverse cutting		Metric	USP	Length	Order number
 <p>3/8 circle</p>	DS 19 mm Easy Pass	1.5	4/0	50 cm	<i>blue</i> 9151519P
		2	3/0	50 cm	<i>blue</i> 9201519P
		3	2/0	50 cm	<i>blue</i> 9301519P
	DS 19 mm black	1	5/0	75 cm	<i>black</i> 9101519VB
		1.5	4/0	75 cm	<i>blue</i> 9151519VB
	DS 24 mm	1	5/0	75 cm	<i>black</i> 9101524
		1.5	4/0	45 cm	<i>blue</i> 9151524-45
		1.5	4/0	75 cm	<i>blue</i> 9151524
		2	3/0	45 cm	<i>blue</i> 9201524-45
		2	3/0	75 cm	<i>blue</i> 9201524
		3	2/0	45 cm	<i>blue</i> 9301524-45
	DS 24 mm Easy Pass	3	2/0	75 cm	<i>blue</i> 9301524
3		2/0	50 cm	<i>blue</i> 9301524P	

Reverse cutting		Metric	USP	Length	Order number
 <p>1/2 circle</p>	HS 17 mm	1.5	4/0	75 cm	<i>blue</i> 9151417
		2	3/0	75 cm	<i>blue</i> 9201417
	HS 22 mm	2	3/0	75 cm	<i>blue</i> 9201422
	HS 26 mm	2	3/0	75 cm	<i>blue</i> 9201426
		3	2/0	75 cm	<i>blue</i> 9301426